Submittal Data

| PROJECT: | UNIT TAG: | QUANTITY: | | |
|-----------------|------------------|-----------|--|--|
| | TYPE OF SERVICE: | | | |
| REPRESENTATIVE: | SUBMITTED BY: | DATE: | | |
| ENGINEER: | APPROVED BY: | DATE: | | |
| CONTRACTOR: | ORDER NO.: | DATE: | | |



DDA 17-7 FCM-C-PV/V/C-F-31U7U7BG


SMART Digital diaphragm dosing pump with internal brushless motor drive. High-end solution for complex and demanding applications (Digital Dosing Advanced).

Note! Product picture may differ from actual product

| Conditions of Service | | | | | |
|-----------------------|-------|--|--|--|--|
| Liquid: | Water | | | | |
| Temperature: | 68 °F | | | | |
| Specific Gravity: | 1.000 | | | | |
| | | | | | |


| Pump Data | | | | | | |
|------------------------------|------------|--|--|--|--|--|
| Maximum operating pressure: | 101.53 psi | | | | | |
| Liquid temperature range: | 32 113 °F | | | | | |
| Maximum ambient temperature: | 113 °F | | | | | |
| Product number: | 93065060 | | | | | |


| Motor Data | | | | | | |
|------------------|----------------|--|--|--|--|--|
| Rated voltage: | 100-240 V | | | | | |
| Mains frequency: | 50 / 60 Hz | | | | | |
| Enclosure class: | IP65 / TYPE 4X | | | | | |
| | | | | | | |




1

Submittal Data







Materials:

Dosing head: PVDF (Polyvinylidene fluoride)

Valve ball: Ceramic Gasket: FKM



Date: 10/02/2025

Qty. | Description

DDA 17-7 FCM-C-PV/V/C-F-31U7U7BG



Note! Product picture may differ from actual product

Product No.: 93065060

The SMART Digital DDA-C is a compact positive-displacement diaphragm dosing pump with variable-speed drive (stepper motor) and intelligent control electronics with minimum energy consumption.

The SMART Digital Dosing series operates at full stroke length to ensure optimum accuracy, priming and suction, even for high-viscosity or degassing liquids.

Depending on the set capacity, the duration of the discharge stroke varies, ensuring an optimal, uniform and continuous discharge flow.

The click-stop mounting plate allows installation in three different positions without using any additional accessories.

The control cube can be easily turned to the front, left or right position.

The click wheel and the multi-coloured backlit graphic plain-text LC display enable intuitive commissioning and operation.

The control elements are protected by a transparent cover.

The DDA-C has built-in connectivity that allows easy setup and tracking via the Grundfos GO app as well as easy integration into a Modbus RTU or TCP bus system.

The sensor-based FlowControlMeasurement (FCM) system detects malfunctions such as air bubbles, line breaks or overpressure directly in the dosing head and displays them in plain text in the alarm menu.

FCM measures the actual pressure and flow rate and eliminates the need for additional monitoring and control devices (accuracy of ± 1.5 % of the set value in a trouble-free process).

The measured pressure and flow are displayed and can be integrated into the process control system, e.g. SCADA.

In addition, the AutoFlowAdapt function automatically adjusts the pump speed to the process conditions to maintain the target flow even with fluctuating back pressure or air bubble formation (degassing drive strategy).

The dosing head includes the following parts:

- · A durable and chemically resistant full PTFE diaphragm,
- Double ball valves for maximum dosing accuracy,
- A deaeration valve for easy start-up,
- A pressure sensor.

Operation modes and functions:

- Manual dosing in ml/h, l/h or gph.
- · Pulse control in ml/pulse (incl. memory function).
- · Analog control, 0/4-20 mA (scalable).
- Pulse-based batch function in ml, I or gal.
- · Timer-based batch function (dosing timer cycle or week).
- Fieldbus control (integrated Modbus RTU and TCP; Profibus DP, Profinet and Ethernet IP via CIM/CIU models).
- Cloud control and monitoring (Smart Digital Chempairing Suite; Grundfos Connect).

Other features:

- The sensor-based FlowControlMeasurement (FCM) system detects malfunctions such as air bubbles, line breaks or overpressure directly in the dosing head.
- Measurement of actual pressure and flow.
- AutoFlowAdapt automatically adjusts the pump speed to the process conditions (what you set is what you get).



Date: 10/02/2025

Qty. | Description

 Degassing drive strategy in case of air bubbles detected in the dosing head and Auto Deaeration during pump standby avoids stand-still due to air-locking.

- · ConditionCheck analyses the pump and the system where the pump is installed.
- Two SlowMode steps (anti-cavitation), 50 % and 25 % maximum flow, e.g. for high-viscosity or degassing liquids.
- Max. Capacity to limit the capacity of the pump to a set maximum.
- Service information display to show when service and which wear-part order numbers are required.
- Two-step key lock function to protect the pump against unauthorised access.
- · Multi-parameter dashboard function to provide further information on up to 4 parameters.
- · Counter for total dosed volume (resettable), operating hours, etc.
- · Save, copy and load customised settings as well as reload factory settings.


Signal inputs/outputs:

- Input for pulse, analog 0/4-20mA, external stop.
- · Input for low-level and empty-tank signal.
- Two potential-free output relays for max. 30 V AC/DC (configurable, e.g. alarm, stroke signal, pump dosing, timer etc.)
- Output analog 0/4-20mA.
- Fieldbus control (Integrated Modbus RTU and TCP; Profibus DP, Profinet and Ethernet IP via CIM/CIU models).
- · Cloud control and monitoring (Smart Digital Chempairing Suite; Grundfos Connect).



Date: 10/02/2025

93065060 DDA 17-7 FCM-C-PV/V/C-F-31U7U7BG





10/02/2025 Date:

| Description | Value |
|--------------------------------------|-------------------------------------|
| General information: | |
| Product name: | DDA 17-7 FCM-C-PV/V/C-F-31U7U7BG |
| Product No: | 93065060 |
| EAN number: | 5715467278576 |
| Technical: | |
| Type key: | DDA 17-7 FCM-C-PV/V/C-F-31U7U7 |
| Max. Flow: | 4.491 US GPH |
| Max. flow in slow mode 50%: | 2.245 US GPH |
| Max. flow in slow mode 25%: | 1.123 US GPH |
| Min flow: | 17.0 ml/h |
| Turn-down ratio: | 1:1000 |
| Approvals: | CE,CSA-US,NSF61,RCM |
| Valve type: | Standard |
| Maximum viscosity at 100 %: | 300 mPas |
| Maximum viscosity in slow mode 50 %: | 1300 mPas |
| Maximum viscosity in slow mode 25 %: | 2000 mPas |
| Accuracy of repeatability: | 1 % |
| Materials: | |
| Dosing head: | PVDF (Polyvinylidene fluoride) |
| Valve ball: | Ceramic |
| Gasket: | FKM |
| Installation: | |
| Range of ambient temperature: | 32 113 °F |
| Maximum operating pressure: | 101.53 psi |
| Installation set (Yes/No): | NO |
| Installation type: | No installation set |
| Pump inlet: | 0.17x 1/4, 1/4x3/8, 3/8x1/2" |
| Pump outlet: | 0.17x 1/4, 1/4x3/8, 3/8x1/2" |
| Max. Suction lift during operation: | 19.7 ft |
| Max. Suction lift during priming: | 9.84 ft |
| Liquid: | |
| Pumped liquid: | Water |
| Liquid temperature range: | 32 113 °F |
| Selected liquid temperature: | 68 °F |
| _ " | 00.00.11.750 |

| H _ [psi] | | | | | | | | | DDA | 17-7 |
|--------------|--------|----------|-------|------------|-------|------|------|------|---------|------|
| | | | | | | | | | | |
| 110 - | | | | | | | | | | |
| 100 | | | | | | | | | | |
| 100 - | | | | | | | | | | |
| 90 - | | | | | | | | | | |
| 55- | | | | | | | | | | |
| 80 - | | | | | | | | | | |
| | | | | | | | | | | |
| 70 - | | | | | | | | | | |
| | | | | | | | | | | |
| 60 - | | | | | | | | | | |
| | | | | | | | | | | |
| 50 - | | | | | | | | | | |
| 40 - | | | | | | | | | | |
| 40 = | | | | | | | | | | |
| 30 - | | | | | | | | | | |
| | | | | | | | | | | |
| 20 - | | | | | | | | | | |
| | | | | | | | | | | |
| 10 - | | | | | | | | | | |
| | | | | | | | | | | |
| 0- | 0. | 5 1 | .0 1 | .5 2. | .0 2. | 5 3. | 0 3. | 5 4. | 0 Q [US | GPH1 |
| | Pumped | liquid = | Water | g operatio | | | | | | , |

Liquid temperature during operation = 68 °F Density = 62.29 lb/ft³



62.29 lb/ft³

Front-Mounted

0/4-20 MA

0/4-20 MA


YES


YES

Yes

YES

2





Density:

Electrical data:

Mains frequency:

Rated voltage:

Length of cable:

Inrush current: Controls:

Control variant: Control panel:

Level control:

Analog input:

Pulse control:

Ext. Stop input:

Analog output:

Output relays:

Others:

Bus communication:




Date: 10/02/2025


| Description | Value |
|--------------------|--------------|
| Net weight: | 6.62 lb |
| Gross weight: | 6.62 lb |
| Color: | RED |
| Country of origin: | US |
| Custom tariff no.: | 8413.19.0000 |




10/02/2025 Date:

93065060 DDA 17-7 FCM-C-PV/V/C-F-31U7U7BG







Note! All units are in [in] unless others are stated. Disclaimer: This simplified dimensional drawing does not show all details.